

2030-34PZB Cut Sheet



igus bracket, 0.98in inside height, 1.5in inside width, 90 to -48 deg pivoting, polyamide, black. For use with 2400 and 2500 series energy chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2030-34PZB>

Technical Specifications

Brand	igus
Item	Bracket
Inside Height	0.98in
Inside Width	1.5in
Rotation Type	90 to -48 deg pivoting
Material	Polyamide
Color	Black
For Use With	2400 and 2500 series energy chain

Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2030-34PZB.pdf>
See store item page for other formats.