

# 2050-12PZB Cut Sheet



igus bracket, 0.98in inside height, 2.24in inside width, 90 deg locking and 0 deg locking, polyamide, black. For use with 2400 and 2500 series energy chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2050-12PZB>

## Technical Specifications

Brand	igus
Item	Bracket
Inside Height	0.98in
Inside Width	2.24in
Rotation Type	90 deg locking and 0 deg locking
Material	Polyamide
Color	Black
For Use With	2400 and 2500 series energy chain

## Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/2050-12PZB.pdf>  
See store item page for other formats.