

# 21517810055 Cut Sheet



Pfannenberg PYRA series audible signal horn, 105 dB at 1m, 150–2900 kHz tone frequency, (80) selectable tone(s), 12–48 VDC, polycarbonate housing, gray, IP66, NEMA 4/4X. For use with Pfannenberg PYRA series pre-assembled bases.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/21517810055>

## Technical Specifications

Brand	Pfannenberg
Item	Audible signal horn
Series	PYRA
Loudness Decibel	105 dB at 1m
Tone Frequency	150–2900 kHz
Tone Type	(80) selectable
Touch to Acknowledge	No
Voltage Rating	12–48 VDC
Housing Material	Polycarbonate
Color	Gray
IP Rating	IP66
NEMA Rating	4/4X
For Use With	Pfannenberg PYRA series pre-assembled bases

## Agency Approvals

UL Listed File #	E189090
UL Recognized File #	NONE
UL Hazardous File #	NONE
CE	<a href="#">View CE declarations</a>
CSA File #	NONE
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/21517810055.pdf>  
See store item page for other formats.