

# 22051 Cut Sheet



Murrelektronik universal surge suppressor, resistor-capacitor, 48-127 VAC/VDC, 1-phase, 0-60Hz, 15W, pigtail with spade connectors, contactor mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/22051>

## Technical Specifications

|                               |  |
|-------------------------------|--|
| <b>Brand</b>                  | Murrelektronik                         |
| <b>Application</b>            | Universal                              |
| <b>Item</b>                   | Surge suppressor                       |
| <b>Circuit Type</b>           | Resistor-capacitor                     |
| <b>Voltage Rating</b>         | 48-127 VAC/VDC                         |
| <b>Number of Phases</b>       | 1                                      |
| <b>Frequency</b>              | 0-60Hz                                 |
| <b>Power Rating</b>           | 15W                                    |
| <b>Connection</b>             | Pigtail with spade connectors          |
| <b>Mounting</b>               | Contactor                              |
| <b>Additional Information</b> | Pigtail for non-contactor applications |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | None                                   |
| <b>UL Recognized File #</b> | E140415                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 080128_0_000                           |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/22051.pdf>  
See store item page for other formats.