

# 221-615 Cut Sheet



WAGO 221 series splicing connector, lever, side-entry, 5 openings, copper conductor, 20-10 AWG solid, 20-10 AWG stranded, 30A, 600V, polycarbonate housing, transparent/orange. Package of 15.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/221-615>

## Technical Specifications

<b>Brand</b>	WAGO
<b>Series</b>	221
<b>Item</b>	Connector
<b>Connector Type</b>	Splicing
<b>Splice Type</b>	Lever
<b>Wiring Direction</b>	Side-entry
<b>Number Of Openings</b>	5
<b>Conductor Material (PF)</b>	Copper

<b>Solid Conductor Size</b>	20-10 AWG
<b>Stranded Conductor Size</b>	20-10 AWG
<b>Amperage Rating</b>	30A
<b>Voltage Rating</b>	600V
<b>Housing Material</b>	Polycarbonate
<b>Housing Color</b>	Transparent/orange
<b>Quantity per Pack</b>	15

## Agency Approvals

<b>UL Listed File #</b>	E69654, E201573
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/221-615.pdf>  
See store item page for other formats.