

23050 Cut Sheet



Murrelektronik motor surge suppressor, resistor-capacitor, 575 VAC, 3-phase, 50/60 Hz, 4 kW, pigtail with spade connectors, adhesive foil mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/23050>

Technical Specifications

Brand	Murrelektronik
Application	Motor
Item	Surge suppressor
Circuit Type	Resistor-capacitor
Voltage Rating	575 VAC
Number of Phases	3
Frequency	50/60 Hz
Power Rating	4 kW
Connection	Pigtail with spade connectors
Mounting	Adhesive foil
Additional Information	Not for use with variable frequency drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E338196
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/23050.pdf>
See store item page for other formats.