

2500-03-075 Cut Sheet



igus 2500 cable drag chain, 0.98in inside height, 1.5in inside width, 2.95in bend radius, outside opening, 1.81in pitch, 3.2ft/1m length, black. Requires 2030-34PZB or 2030-12PZB brackets for mounting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2500-03-075>

Technical Specifications

Brand	igus
Series	2500
Item	Cable drag chain
Inside Height	0.98in
Inside Width	1.5in
Bend Radius	2.95in
Opening	Outside
Pitch	1.81in
Length	3.2ft/1m
Color	Black
Requires	2030-34PZB or 2030-12PZB brackets for mounting

Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/2500-03-075.pdf>
See store item page for other formats.