

# 2500-07-100 Cut Sheet



igus 2500 cable drag chain, 0.98in inside height, 3.03in inside width, 3.94in bend radius, outside opening, 1.81in pitch, 3.2ft/1m length, black. Requires 2070-34PZB or 2070-12PZB brackets for mounting.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2500-07-100>

## Technical Specifications

Brand	igus
Series	2500
Item	Cable drag chain
Inside Height	0.98in
Inside Width	3.03in
Bend Radius	3.94in
Opening	Outside
Pitch	1.81in
Length	3.2ft/1m
Color	Black
Requires	2070-34PZB or 2070-12PZB brackets for mounting

## Agency Approvals

RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	<a href="#">View EU REACH document</a>
Other	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/2500-07-100.pdf>  
See store item page for other formats.