

# 2773-404 Cut Sheet



WAGO 2773 series splicing connector, push-in, side-entry, 4 openings, copper conductor, 20-12 AWG solid, 18-12 AWG stranded, 20A, 600V, polycarbonate housing, transparent/red. Package of 80.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2773-404>

## Technical Specifications

<b>Brand</b>	WAGO
<b>Series</b>	2773
<b>Item</b>	Connector
<b>Connector Type</b>	Splicing
<b>Splice Type</b>	Push-in
<b>Wiring Direction</b>	Side-entry
<b>Number Of Openings</b>	4
<b>Conductor Material (PF)</b>	Copper

<b>Solid Conductor Size</b>	20-12 AWG
<b>Stranded Conductor Size</b>	18-12 AWG
<b>Amperage Rating</b>	20A
<b>Voltage Rating</b>	600V
<b>Housing Material</b>	Polycarbonate
<b>Housing Color</b>	Transparent/red
<b>Quantity per Pack</b>	80

## Agency Approvals

<b>UL Listed File #</b>	E69654, E201573
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/2773-404.pdf>  
See store item page for other formats.