

2787-2448 Cut Sheet



WAGO Pro2 series switching power supply, 24 VDC @ 40A/960W (adjustable), 220 VAC nominal input, 1-phase, enclosed, metal housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2787-2448>

Technical Specifications

Brand	WAGO
Item	Power supply
Series	Pro2
Power Supply Type	Switching
Efficiency	96% @230VAC
Output Configuration	Single output
Output	24 VDC @ 40A/960W (adjustable)
Output Voltage Range	24-28 VDC
Input voltage range	180-264 VAC/255-373 VDC
Number of Input Phases	1
Protection Type(s)	<ul style="list-style-type: none">• overvoltage• short circuit

Voltage Monitoring	Yes
Enclosure Type	Enclosed
Housing Material	Metal
IP Rating	IP20
Mounting	35mm DIN rail
Connector Type	Cage clamp
NEC Class 2	No
Integrated UPS Battery Control	No
Operating Temperature	-20 to 75 deg C
Power Boost	150% for 5s

Agency Approvals

UL Listed File #	E255817
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2787-2448.pdf>
See store item page for other formats.