

29112 Cut Sheet



METE female insert, connector housing size 24B, 12-pole, screw terminals, accepts wire size 6-16 AWG, 26-14 AWG, 80 amp (4-pole), 16 amp (8-pole), 600 VAC/VDC, poles numbered 1 to 12. For use with METE multi-wire housings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/29112>

Technical Specifications

| | |
|-------------------------------|----------------------------------|
| Brand | METE |
| Item | Female Insert |
| Connector Housing Size | 24B |
| Number of Poles | 12 |
| Termination Type | Screw terminals |
| Wire Size | 6-16 AWG, 26-14 AWG |
| Amperage Rating | 80 amp (4-pole), 16 amp (8-pole) |
| Voltage Rating | 600 VAC/VDC |
| Pole Marking | Numbered 1 to 12 |
| For Use With | METE multi-wire housings |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | In progress |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/29112.pdf>
See store item page for other formats.