

29420 Cut Sheet



METE female insert, connector housing size 10A, 10-pole, screw terminals, accepts wire size 18-14 AWG, 16 amp, 600 VAC/VDC, poles numbered 1 to 10. For use with METE multi-wire housings.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/29420>

Technical Specifications

Brand	METE
Item	Female Insert
Connector Housing Size	10A
Number of Poles	10
Termination Type	Screw terminals
Wire Size	18-14 AWG
Amperage Rating	16 amp
Voltage Rating	600 VAC/VDC
Pole Marking	Numbered 1 to 10
For Use With	METE multi-wire housings

Agency Approvals

UL Listed File #	None
UL Recognized File #	E307105
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/29420.pdf>
See store item page for other formats.