

# 2CSC2036 Cut Sheet



Hammond operator console, NEMA 3R/4/4X/12, 38 x 36 x 20in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush oil-tight stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2CSC2036>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Item</b>	Operator console
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	3R/4/4X/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	38 x 36 x 20in (HxWxD)
<b>Enclosure Height</b>	38.81in
<b>Enclosure Width</b>	36.00in
<b>Enclosure Depth</b>	21.03in
<b>Mounting</b>	Freestanding
<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	No

<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Bottom Gland Plate</b>	No
<b>Material</b>	304 stainless steel
<b>Finish</b>	#4 brush
<b>Cover Type</b>	Single-door
<b>Hinge Type</b>	Cast hinge with removable pin
<b>Number of Hinges Per Door</b>	2
<b>Number of Lid Hinges</b>	3
<b>Latch Type</b>	1/4-turn semi-flush oil-tight stainless steel latch
<b>Number of Door Latches</b>	2
<b>Number of Lid Latches</b>	2
<b>Shelf</b>	No
<b>Padlockable</b>	No
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E65324
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR21001
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2CSC2036.pdf>  
See store item page for other formats.