

2CSC2060 Cut Sheet



Hammond operator console, NEMA 3R/4/4X/12, 38 x 60 x 20in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, 2-door, 1/4-turn semi-flush oil-tight stainless steel latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2CSC2060>

Technical Specifications

Brand	Hammond
Item	Operator console
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12
IP Rating	IP66
Nominal Enclosure Dimensions	38 x 60 x 20in (HxWxD)
Enclosure Height	38.81in
Enclosure Width	60.00in
Enclosure Depth	21.03in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	2-door
Hinge Type	Cast hinge with removable pin
Number of Hinges Per Door	2
Number of Lid Hinges	4
Latch Type	1/4-turn semi-flush oil-tight stainless steel latch
Number of Door Latches	4
Number of Lid Latches	3
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2CSC2060.pdf>
See store item page for other formats.