

3200303 Cut Sheet



Seifert SoliTherm thermoelectric cooler, 680 BTU/H, 24 VDC operating voltage, 304 stainless steel housing, filter-free, recessed mount. For use with NEMA 4/4X/12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3200303>

Technical Specifications

| | |
|---------------------------------|-----------------------|
| Brand | Seifert |
| Series | SoliTherm |
| Item | Thermoelectric cooler |
| Nominal Cooling Capacity | 680 BTU/H |
| Operating Voltage | 24 VDC |
| Running Current | 11.6A |
| Height | 15.75in |
| Width | 7.09in |

| | |
|-------------------------|-------------------------|
| Depth | 6.73in |
| Mounting | Recessed |
| Filter-Free | Yes |
| Housing Material | 304 stainless steel |
| IP Rating | IP66 |
| For Use With | NEMA 4/4X/12 enclosures |
| Includes | Mounting hardware |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | SA32278 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3200303.pdf>
See store item page for other formats.