

3410-2000 Cut Sheet



Trumeter electrical hour meter, 7mm 8-digit LCD, 10-300 VDC or 20-300 VAC input, rectangular flush mount with clip, 1/4in (6.4mm) spade terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3410-2000>

Technical Specifications

Brand	Trumeter
Item	Hour meter
Counter Type	Electrical
Count Direction	Up
Display Type	LCD
Display Size	7mm 8-digit
Display Units	Hours and tenths
Input Signal	10-300 VDC or 20-300 VAC
Mounting	Panel
Mounting Type	Rectangular flush mount with clip

Mounting Hole Size	1.46 x 0.94in
Connector Type	1/4in (6.4mm) spade terminals
Additional Information	NEMA 4/4X, 12 & IP66 compliant from the front when using the optional gasket
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Battery• Battery Type: Other• Generic Battery: CR2032

Agency Approvals

UL Listed File #	None
UL Recognized File #	E36690
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3410-2000.pdf>
See store item page for other formats.