

3425-8 Cut Sheet



RACO connector, liquid-tight, 90-degree, 1-1/4in trade size, 1-1/4in NPT thread type, zinc electro-plated finish. For use with Liquatite electrical conduit. Sealing washer and locknut included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/3425-8>

Technical Specifications

Brand	RACO
Item	Connector
Liquid-tight	Yes
Connector Type	90-degree
Material	Malleable iron
Trade Size	1-1/4in
Thread Type	1-1/4in NPT
Insulation	No
Finish	Zinc electro-plated
For Use With	Liquatite electrical conduit
Includes	Sealing washer and locknut

Agency Approvals

UL Listed File #	E195969
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	1456072
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/3425-8.pdf>
See store item page for other formats.