

38059 Cut Sheet



FTG enclosed terminal block, finger-safe, 840A, 1-pole, line side: 2 openings accept 600 kcmil to 4 AWG, load side: 2 openings accept 600 kcmil to 4 AWG, panel or 35mm DIN rail mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38059>

Technical Specifications

Brand	FTG
Item	Terminal block
Terminal Block Type	Enclosed
Modular	No
Finger-safe	Yes
Amperage Rating	840A
Number of Poles	1
Line Side Openings	2 openings accept 600 kcmil to 4 AWG
Load Side Openings	2 openings accept 600 kcmil to 4 AWG
Mounting	Panel or 35mm DIN rail
SCCR Rating	10kA SCCR
UL Rating	UL 1059 recognized
IP Rating	IP20

Agency Approvals

UL Recognized File #	E98082
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/38059.pdf>
See store item page for other formats.