

38641 Cut Sheet



FTG enclosed terminal block, finger-safe, 115A, 1-pole, line side: 1 opening accepts 2 AWG to 8 AWG & 1 opening accepts 4 AWG to 14 AWG, load side: 6 openings accept 4 AWG to 14 AWG, panel or 35mm DIN rail mount, UL 1059 recognized.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38641>

Technical Specifications

| | |
|----------------------------|---|
| Brand | FTG |
| Item | Terminal block |
| Terminal Block Type | Enclosed |
| Modular | No |
| Finger-safe | Yes |
| Amperage Rating | 115A |
| Number of Poles | 1 |
| Line Side Openings | 1 opening accepts 2 AWG to 8 AWG & 1 opening accepts 4 AWG to 14 AWG |
| Load Side Openings | 6 openings accept 4 AWG to 14 AWG |
| Mounting | Panel or 35mm DIN rail |
| SCCR Rating | 10kA SCCR |
| UL Rating | UL 1059 recognized |
| IP Rating | IP20 |

Agency Approvals

| | |
|-----------------------------|--|
| UL Recognized File # | E98082 |
| CE | View CE declarations |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/38641.pdf>
See store item page for other formats.