

38680C Cut Sheet



FTG enclosed power distribution block, finger-safe, 85A, 1-pole, line side: 1 opening accepts 3 AWG to 14 AWG, load side: 6 openings accept 8 AWG to 14 AWG, panel or 35mm DIN rail mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38680C>

Technical Specifications

Brand	FTG
Item	Power distribution block
Terminal Block Type	Enclosed
Modular	Yes
Finger-safe	Yes
Amperage Rating	85A
Number of Poles	1
Line Side Openings	1 opening accepts 3 AWG to 14 AWG
Load Side Openings	6 openings accept 8 AWG to 14 AWG
Mounting	Panel or 35mm DIN rail
SCCR Rating	100kA SCCR
UL Rating	UL 1953 listed
IP Rating	IP20
Additional Information	Suitable for branch and feeder circuits

Agency Approvals

UL Listed File #	E483207
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/38680C.pdf>
See store item page for other formats.