

# 38688C Cut Sheet



FTG enclosed power distribution block, finger-safe, 380A, 1-pole, line side: 1 opening accepts 500 kcmil to 2/0 AWG, load side: 6 openings accept 2 AWG to 14 AWG, panel or 35mm DIN rail mount, UL 1953 listed.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/38688C>

## Technical Specifications

<b>Brand</b>	FTG
<b>Item</b>	Power distribution block
<b>Terminal Block Type</b>	Enclosed
<b>Modular</b>	Yes
<b>Finger-safe</b>	Yes
<b>Amperage Rating</b>	380A
<b>Number of Poles</b>	1
<b>Line Side Openings</b>	1 opening accepts 500 kcmil to 2/0 AWG
<b>Load Side Openings</b>	6 openings accept 2 AWG to 14 AWG
<b>Mounting</b>	Panel or 35mm DIN rail
<b>SCCR Rating</b>	100kA SCCR
<b>UL Rating</b>	UL 1953 listed
<b>IP Rating</b>	IP20
<b>Additional Information</b>	Suitable for branch and feeder circuits

## Agency Approvals

<b>UL Listed File #</b>	E483207
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/38688C.pdf>  
See store item page for other formats.