

416-1201-000 Cut Sheet



Jefferson Electric buck-boost transformer, encapsulated core, 100VA, 1-phase, 120/240 VAC, 16/32 VAC secondary, 60 Hz, NEMA 3R, wall mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/416-1201-000>

Technical Specifications

Brand	Jefferson Electric
Item	Transformer
Transformer Type	Buck-boost
Core Type	Encapsulated
Power Rating	100VA
Number of Phases	1
Primary Voltage	120/240 VAC
Secondary Voltage	16/32 VAC
Frequency	60 Hz
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Wall
Application	Suitable for use as auto or isolation transformer

Agency Approvals

UL Listed File #	E4466
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/416-1201-000.pdf>
See store item page for other formats.