

# 4825U200 Cut Sheet



Socomec DIRIS A20 power meter, current and voltage input, 3-line backlit LCD, optional plug-in modules for output, 110-240 VAC/120-250 VDC operating voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/4825U200>

## Technical Specifications

<b>Brand</b>	Socomec
<b>Item</b>	Power meter
<b>Series</b>	DIRIS A20
<b>Display Type</b>	3-line backlit LCD
<b>Input Current Signal Range</b>	0-5A
<b>Input Voltage Signal Range</b>	50-500 VAC (L-L), 28-289 VAC (L-N)
<b>Operating Voltage</b>	110-240 VAC/120-250 VDC
<b>Accuracy</b>	0.5% active power
<b>System Configuration</b>	1-phase, 2-phase, 3-phase 3-wire, 3-phase 4-wire
<b>Mounting</b>	Panel
<b>Mounting Hole Size</b>	92mm x 92mm
<b>Additional Information</b>	An integrated test function can be utilized to detect incorrect wiring, accepts up to 2 output or communication plugin modules

## Agency Approvals

<b>UL Listed File #</b>	E257746
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>