

5U24S104 Cut Sheet



Metal Work pressure switch, air, 1/2in female NPT process connection, 7.5 to 145 psi set point, N.O./N.C. complementary, 2m 3-wire cable. For use with Syntesi Size 2 air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U24S104>

Technical Specifications

Brand	Metal Work
Item	Pressure switch
Working Fluid	Air
Process Connection	1/2in female NPT
Setpoint Range	7.5 to 145 psi
Output	N.O./N.C. complementary
Electrical Connection	2m 3-wire cable
For Use With	Syntesi Size 2 air prep components
Additional Information	(2) plugged G1/4 female BSPP outlet ports

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/5U24S104.pdf>
See store item page for other formats.