

# 5U25V705 Cut Sheet



Metal Work shut-off valve, 3-port (3-way), 2-position, single solenoid spring return, N.C., 3/4in female NPT inlet(s), 3/4in female NPT outlet(s), G1/4 female BSPP exhaust(s), Cv=4.4. For use with Syntesi Size 2 air prep components.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/5U25V705>

## Technical Specifications

<b>Brand</b>	Metal Work
<b>Series</b>	Syntesi Size 2
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Shut-off
<b>Action</b>	Single solenoid spring return
<b>Manual Override Type</b>	Locking
<b>Port Quantity</b>	3-port (3-way)
<b>Number Of Positions</b>	2

<b>Valve Configuration</b>	N.C.
<b>Inlet Port</b>	3/4in female NPT
<b>Outlet Port</b>	3/4in female NPT
<b>Exhaust Port</b>	G1/4 female BSPP
<b>Flow Coefficient</b>	4.4
<b>For Use With</b>	Syntesi Size 2 air prep components
<b>Additional Information</b>	Purchase solenoid coil in desired voltage separately. (2) plugged G1/4 female BSPP outlet ports

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/5U25V705.pdf>  
See store item page for other formats.