

65701055 Cut Sheet



WERMA eSIGN series LED signal tower, black, (9) tiers, 72mm diameter, custom programmable colors, selectable multi light function, 24 VDC, 360 degree viewing angle, 4-pin M12 A-coded (IO-Link), base or tube mount, IP66 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/65701055>

Technical Specifications

Brand	WERMA
Item	Signal tower
Bulb Type	LED
Series	ESIGN
Number of Pre-Assembled Tiers	9
Diameter	72mm
Light Color(s)	Custom programmable colors
Light Function	Selectable permanent, blinking, flashing, double flash, triple flash or rotating
Communication Port and Connection Type(s)	(1) 4-pin M12 A-coded (IO-Link)
Port Protocol(s)	IO-Link Class A Device
Port Speed(s)	IO-Link COM3

IO-Link Version	IO-Link v1.1
Standard I/O Mode Supported	Yes
Voltage Rating	24 VDC
Lens Type	Clear
Body Length	271mm
Body Color	Black
Body Material	Polycarbonate
Tower Viewing Angle	360 degree
Connector Type	4-pin M12 A-coded (IO-Link)
Mounting	Base or tube
IP Rating	IP66 and IP69K

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	Clean Room Certification ISO 14644-14

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/65701055.pdf>
See store item page for other formats.