

65710055 Cut Sheet



WERMA eSIGN series LED signal tower, black, (9) tiers, 72mm diameter, custom programmable colors, selectable multi light function, (10) selectable tone(s), 24 VDC, 360 degree viewing angle, 8-pin M12 A-coded, base or tube mount, IP66 and IP69K.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/65710055>

Technical Specifications

| | |
|--------------------------------------|--|
| Brand | WERMA |
| Item | Signal tower |
| Bulb Type | LED |
| Series | ESIGN |
| Number of Pre-Assembled Tiers | 9 |
| Diameter | 72mm |
| Light Color(s) | Custom programmable colors |
| Light Function | Selectable permanent, blinking, flashing, double flash, triple flash or rotating |
| Number of Alarms | 10 |
| Loudness Decibel | 105 dB at 1m |
| Tone Frequency | 900 Hz to 3.6 kHz |

| | |
|--|-------------------|
| Tone Type | (10) selectable |
| Communication Port and Connection Type(s) | (1) USB C |
| Voltage Rating | 24 VDC |
| Lens Type | Clear |
| Body Length | 271mm |
| Body Color | Black |
| Body Material | Polycarbonate |
| Tower Viewing Angle | 360 degree |
| Connector Type | 8-pin M12 A-coded |
| Mounting | Base or tube |
| IP Rating | IP66 and IP69K |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E164155 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | Clean Room Certification ISO 14644-14 |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/65710055.pdf>
See store item page for other formats.