

7000-08325-0000000 Cut Sheet



Murrelektronik connector, field-wireable, 3-pin M8 axial male A-coded, accepts cable diameter size 2.5-5mm, 24-20 AWG, insulation displacement (IDC) connection, IP65 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-08325-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Type	M8
Coding	A coding
Gender	Male with male threads
Angle	Axial

Number of Pins	3
Terminal Connection	Insulation displacement (IDC)
Cable Diameter Size	2.5-5mm
Conductor Size	24-20 AWG
Shielded	No
Housing Material	Nylon
IP Rating	IP65 IP67

Agency Approvals

UL Listed File #	n/a
UL Recognized File #	E224242
CE	View CE declarations
CSA File #	n/a
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-08325-0000000.pdf>
See store item page for other formats.