

7000-13911-0000000 Cut Sheet



Murrelektronik connector, field-wireable, 5-pin M12 90-degree male A-coded, accepts cable diameter size 4-8mm, 26-18 AWG, push-lock spring clamp connection, IP65 IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-13911-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Connector Type	M12
Coding	A-coded
Gender	Male
Angle	90-degree
Number of Pins	5
Terminal Connection	Push-lock spring clamp
Cable Diameter Size	4-8mm
Conductor Size	26-18 AWG
Shielded	No
Housing Material	Polyamide
IP Rating	IP65 IP67

Agency Approvals

UL Listed File #	E325311
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-13911-0000000.pdf>
See store item page for other formats.