

7000-14521-0000000 Cut Sheet



Murrelektronik field wireable Ethernet connector, M12 D-coded 4-pole male axial, accepts cable diameter size 4.5-8.8mm, 26-22 AWG, insulation displacement (IDC) connection, shielded, IP65 IP67. Exceeds Category 5E specifications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-14521-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Field wireable Ethernet connector
Connector Type	M12 D-coded 4-pole male axial
Cable Diameter Size	4.5-8.8mm
Conductor Size	26-22 AWG
Terminal Connection	Insulation displacement (IDC)
Shielded	Yes
IP Rating	IP65 IP67
Additional Information	Exceeds Category 5E specifications

Agency Approvals

UL Listed File #	None
UL Recognized File #	E224242
UL Hazardous File #	None
CE	None
CSA File #	1781018
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement