

# 7000-17341-0000000 Cut Sheet



Murrelektronik connector, field-wireable, M12 barrel 8-pin male axial connection, accepts cable diameter size 6-8mm, 20 AWG, screw terminal connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-17341-0000000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Connector
<b>Field-Wireable</b>	Yes
<b>Form Factor</b>	Cable termination
<b>Connector Type</b>	M12
<b>Coding</b>	A-coded
<b>Gender</b>	Male with male threads
<b>Angle</b>	Axial

<b>Number of Wires</b>	8
<b>Number Of Pins</b>	8
<b>Terminal Connection</b>	Screw terminal
<b>Cable Diameter Size</b>	6-8mm
<b>Conductor Size</b>	20 AWG
<b>Shielded</b>	Yes
<b>Housing Material</b>	Nickel plated brass
<b>IP Rating</b>	IP67

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	080128_0_000
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-17341-0000000.pdf>  
See store item page for other formats.