


7000-19162-9790050 Cut Sheet



Murrelektronik bulkhead connector, M12 male 12-pin to pigtail, 26 AWG, 1.6ft/0.5m cable length, nylon 12 conductor insulation material, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-19162-9790050>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Form Factor	Bulkhead
Connection 1	M12 male with male threads 12-wire/12-pin
Connection 2	Pigtail
Shielded	No
Cable Length	1.6ft/0.5m

Conductor Size	26 AWG
Conductor Insulation Material	Nylon 12
Housing Material	Nickel plated brass
IP Rating	IP67
Includes	Mounting nut(s)

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	1781018
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-19162-9790050.pdf>
See store item page for other formats.