

# 7000-40521-2420300 Cut Sheet



Murrelektronik connection cable, M12 axial male A-coded to M12 axial female A-coded, 5-pole, 60 VAC/VDC, 4A, 22 AWG, PUR jacket, gray, shielded, 9.8ft/3m cable length, IP65 IP66K IP67, sensor & signal and drag chain.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-40521-2420300>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Cable
<b>Cable Type</b>	Connection
<b>Connection 1</b>	M12 axial male with male threads A-coded
<b>Connection 2</b>	M12 axial female with female threads A-coded
<b>Number of Poles</b>	5
<b>Voltage Rating</b>	60 VAC/VDC
<b>Amperage Rating</b>	4A

<b>Conductor Size</b>	22 AWG
<b>Jacket Material</b>	PUR
<b>Jacket Color</b>	Gray
<b>Shield Type</b>	Shielded
<b>Cable Length</b>	9.8ft/3m
<b>IP Rating</b>	IP65 IP66K IP67
<b>Application</b>	Sensor & signal and drag chain

## Agency Approvals

<b>UL Listed File #</b>	E325311
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	080128-0-000
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-40521-2420300.pdf>  
See store item page for other formats.