

7000-74011-0000000 Cut Sheet



Murrelektronik Cat6a Ethernet connector, field-wireable, RJ45 8-pole Ethernet male axial, accepts cable diameter size 4.5-9mm, 26-22 AWG, insulation displacement (IDC) connection, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-74011-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Standard	Cat6a Ethernet
Connector Type	RJ45
Gender	Male
Angle	Axial

Number of Pins	8
Terminal Connection	Insulation displacement (IDC)
Cable Diameter Size	4.5-9mm
Conductor Size	26-22 AWG
Shielded	Yes
Housing Material	PVC/polyethylene
IP Rating	IP20
Additional Information	Exceeds Category 6A specifications

Agency Approvals

UL Listed File #	None
UL Recognized File #	E224242
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-74011-0000000.pdf>
See store item page for other formats.