

# 7000-74031-0000000 Cut Sheet



Murrelektronik Cat6a Ethernet connector, field-wireable, RJ45 8-pole Ethernet male 45-degree, accepts cable diameter size 4.5-8mm, 26-22 AWG, insulation displacement (IDC) connection, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-74031-0000000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Connector
<b>Field-Wireable</b>	Yes
<b>Form Factor</b>	Cable termination
<b>Connector Standard</b>	Cat6a Ethernet
<b>Connector Type</b>	RJ45
<b>Gender</b>	Male
<b>Angle</b>	45-degree

<b>Number of Pins</b>	8
<b>Terminal Connection</b>	Insulation displacement (IDC)
<b>Cable Diameter Size</b>	4.5-8mm
<b>Conductor Size</b>	26-22 AWG
<b>Shielded</b>	Yes
<b>Housing Material</b>	PVC/polyethylene
<b>IP Rating</b>	IP20
<b>Additional Information</b>	Exceeds Category 6A specifications

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E224242
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-74031-0000000.pdf>  
See store item page for other formats.