

7000-74075-0000000 Cut Sheet



Murrelektronik Cat5e Ethernet connector, field-wireable, 8-pin RJ45 axial male heavy duty, accepts cable diameter size 5-9mm, 24-26 AWG, insulation displacement (IDC) connection, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-74075-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Standard	Cat5e Ethernet
Connector Type	RJ45
Gender	Male
Angle	90-degree
Number of Pins	8

Terminal Connection	Insulation displacement (IDC)
Cable Diameter Size	5-9mm
Conductor Size	24-26 AWG
Shielded	Yes
Housing Material	Die-cast zinc
IP Rating	IP20
Additional Information	Use with Cat5 & Cat5e cable, transfer rate up to 1 Gbit/s

Agency Approvals

UL Listed File #	E362618
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/7000-74075-0000000.pdf>
See store item page for other formats.