

7000-78061-0000000 Cut Sheet



Murrelektronik connector, field-wireable, 7/8in - 16 UN2 axial male with male threads, accepts cable diameter size 6-8mm, 16 AWG, screw terminal connection, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-78061-0000000>

Technical Specifications

Brand	Murrelektronik
Item	Connector
Field-Wireable	Yes
Form Factor	Cable termination
Connector Type	7/8in
Gender	Male
Angle	Axial

Number of Pins	4
Terminal Connection	Screw terminal
Cable Diameter Size	6-8mm
Conductor Size	16 AWG
Shielded	No
Housing Material	Thermoplastic (PBT)
IP Rating	IP67

Agency Approvals

UL Listed File #	NA
UL Recognized File #	E325311
CE	None
CSA File #	n/a
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7000-78061-0000000.pdf>
See store item page for other formats.