

# 7000-P4661-0000000 Cut Sheet



Murrelektronik connector, field-wireable, 5-pin M12 axial female L-coded, accepts cable diameter size 9-13mm, 16-14 AWG, push-lock spring clamp connection, IP65.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7000-P4661-0000000>

## Technical Specifications

<b>Brand</b>	Murrelektronik
<b>Item</b>	Connector
<b>Field-Wireable</b>	Yes
<b>Connector Type</b>	M12
<b>Coding</b>	L-coded
<b>Gender</b>	Female
<b>Angle</b>	Axial
<b>Number of Pins</b>	5
<b>Terminal Connection</b>	Push-lock spring clamp
<b>Cable Diameter Size</b>	9-13mm
<b>Conductor Size</b>	16-14 AWG
<b>Shielded</b>	No
<b>Housing Material</b>	Nickel-plated brass
<b>IP Rating</b>	IP65

## Agency Approvals

<b>UL Listed File #</b>	E325311
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7000-P4661-0000000.pdf>  
See store item page for other formats.