

# 722-0004 Cut Sheet



Trumeter electromechanical hour meter, 3.6mm 6-digit analog, 90-264 VAC input, round 3-hole mount, 1/4in (6.4mm) spade terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/722-0004>

## Technical Specifications

<b>Brand</b>	Trumeter
<b>Item</b>	Hour meter
<b>Counter Type</b>	Electromechanical
<b>Count Direction</b>	Up
<b>Display Type</b>	Analog
<b>Display Size</b>	3.6mm 6-digit
<b>Display Units</b>	Hours and tenths
<b>Input</b>	90-264 VAC
<b>Operating Voltage</b>	90-264 VAC
<b>Mounting</b>	Panel
<b>Mounting Type</b>	Round 3-hole mount
<b>Mounting Hole Size</b>	2.0in diameter
<b>Connector Type</b>	1/4in (6.4mm) spade terminals
<b>Additional Information</b>	NEMA 4/4X compliant from the front when using the optional gasket

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E123666
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>