

7231-13541-9710050 Cut Sheet



Murrelektronik bulkhead connector, M12 4-wire female to pigtail, 22 AWG, 1.6ft/0.5m cable length, nylon 12 conductor insulation material, IP67.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7231-13541-9710050>

Technical Specifications

| | |
|---------------------|---|
| Brand | Murrelektronik |
| Item | Connector |
| Form Factor | Bulkhead |
| Connection 1 | M12 female with female threads 4-wire/5-pin |
| Connection 2 | Pigtail |
| Shielded | No |

| | |
|--------------------------------------|-----------------------------|
| Cable Length | 1.6ft/0.5m |
| Conductor Size | 22 AWG |
| Conductor Insulation Material | Nylon 12 |
| Housing Material | Nickel-plated die-cast zinc |
| IP Rating | IP67 |
| Includes | Mounting nut(s) |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | E224242 |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 080128_0_000 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7231-13541-9710050.pdf>
See store item page for other formats.