

7700-44711-S7V0200 Cut Sheet



Murrelektronik Cat5e Ethernet connection cable, M12 axial male D-coded to RJ45 axial male, 4-pole, 60 VDC, 1.5A, 22 AWG, TPE jacket, green, overall aluminum foil and tinned copper braid, 6.5ft/2m cable length, IP67 (M12) IP20 (RJ45), data.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-44711-S7V0200>

Technical Specifications

Brand	Murrelektronik
Item	Cable
Cable Type	Cat5e Ethernet connection
Connection 1	M12 axial male with male threads D-coded
Connection 2	RJ45 axial male
Number of Poles	4
Voltage Rating	60 VDC
Amperage Rating	1.5A
Conductor Size	22 AWG

Jacket Material	TPE
Jacket Color	Green
Shield Type	Overall aluminum foil and tinned copper braid
Cable Length	6.5ft/2m
IP Rating	IP67 (M12) IP20 (RJ45)
Application	Data
For Use With	10/100 Mbps networks
Additional Information	CAT5e ISO/IEC 11801, (Class D bis 100 MBit/s)

Agency Approvals

UL Listed File #	E325311
UL Recognized File #	n/a
CE	View CE declarations
CSA File #	n/a
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/7700-44711-S7V0200.pdf>
See store item page for other formats.