

# 7700-A4011-U0C0100 Cut Sheet



Murrelektronik connection cable, 7/8in - 16 UN2 90-degree male with male threads to Pigtail with European Color Code, 4-pole, 600 VAC/VDC, 9A, 16 AWG, TPE jacket, yellow, unshielded, 3.2ft/1m cable length, IP68, power.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/7700-A4011-U0C0100>

## Technical Specifications

|                        |                                                 |
|------------------------|-------------------------------------------------|
| <b>Brand</b>           | Murrelektronik                                  |
| <b>Item</b>            | Cable                                           |
| <b>Cable Type</b>      | Connection                                      |
| <b>Connection 1</b>    | 7/8in - 16 UN2 90-degree male with male threads |
| <b>Connection 2</b>    | Pigtail with European Color Code                |
| <b>Number of Poles</b> | 4                                               |
| <b>Voltage Rating</b>  | 600 VAC/VDC                                     |
| <b>Amperage Rating</b> | 9A                                              |

|                        |            |
|------------------------|------------|
| <b>Conductor Size</b>  | 16 AWG     |
| <b>Jacket Material</b> | TPE        |
| <b>Jacket Color</b>    | Yellow     |
| <b>Shield Type</b>     | Unshielded |
| <b>Cable Length</b>    | 3.2ft/1m   |
| <b>IP Rating</b>       | IP68       |
| <b>Application</b>     | Power      |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | E325311                                                             |
| <b>UL Recognized File #</b> | NA                                                                  |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | n/a                                                                 |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/7700-A4011-U0C0100.pdf>  
See store item page for other formats.