

787-1662-006-1000 Cut Sheet



WAGO electronic circuit protector, current-limiting, adjustable 0.5-6A, 24 VDC, 2 independent channel(s), 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/787-1662-006-1000>

Technical Specifications

| | |
|----------------------|--------------------|
| Brand | WAGO |
| Item | Circuit protector |
| Circuit Breaker Type | Compact |
| Circuit Type | Supplementary |
| Current-Limiting | Yes |
| Amperage Rating | Adjustable 0.5-6A |
| Input voltage range | 18-30 VDC |
| Output Voltage Range | 18-30 VDC |
| Channels | 2 independent |
| Trip Type | Electronic |
| Reset | Remote or local |
| Mounting | 35mm DIN rail |
| Connection | Push-in cage clamp |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E255817 |
| UL Recognized File # | E363438 |
| UL Hazardous File # | NONE |
| CE | View CE declarations |
| CSA File # | NONE |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |
| Other | DNV GL Approval |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/787-1662-006-1000.pdf>
See store item page for other formats.