

8000-84160-0000000 Cut Sheet



Exact 8 passive distribution block, 4 ports, 4-pin M8 sockets, 4-wire, 24 VDC, 1A, power and PNP LED indicator(s), 12-pin M12 quick-disconnect, IP67. Marking tags included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8000-84160-0000000>

Technical Specifications

| | |
|------------------|----------------------------|
| Brand | Exact 8 |
| Item | Passive distribution block |
| Number of Ports | 4 |
| Socket Type | 4-pin M8 |
| Wires Per Socket | 4-wire |
| Socket Current | 1A |
| I/O Per Socket | 2 |

| | |
|-------------------|-----------------------------|
| Voltage Rating | 24 VDC |
| Number Of Commons | 1 |
| Indicator | Power and PNP LED |
| Connector Type | 12-pin M12 quick-disconnect |
| IP Rating | IP67 |
| Includes | Marking tags |

Agency Approvals

| | |
|----------------------|---|
| UL Listed File # | E201820 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/8000-84160-0000000.pdf>
See store item page for other formats.