

8000-88110-3950500 Cut Sheet



Exact 8 passive distribution block, 8 ports, 4-pin M8 sockets, 4-wire, 24 VDC, 2A, power and PNP LED indicator(s), 5m integrated cable, IP67. Marking tags included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8000-88110-3950500>

Technical Specifications

Brand	Exact 8
Item	Passive distribution block
Number of Ports	8
Socket Type	4-pin M8
Wires Per Socket	4-wire
Socket Current	2A
I/O Per Socket	2

Voltage Rating	24 VDC
Number Of Commons	1
Load Current	8A/common
Indicator	Power and PNP LED
Connector Type	5m integrated cable
IP Rating	IP67
Includes	Marking tags

Agency Approvals

UL Listed File #	E201820
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/8000-88110-3950500.pdf>
See store item page for other formats.