


8000-88460-0000000 Cut Sheet



Exact 12 passive distribution block, 8 ports, 5-pin M12 sockets, (2) 5-wire and (6) 4-wire, 24 VDC, 1A, power and PNP LED indicator(s), 12-pin M12 quick-disconnect, IP67. Marking tags included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8000-88460-0000000>

Technical Specifications

Brand	Exact 12
Item	Passive distribution block
Number of Ports	8
Socket Type	5-pin M12
Wires Per Socket	(2) 5-wire and (6) 4-wire
Socket Current	1A
I/O Per Socket	1
Voltage Rating	24 VDC
Number Of Commons	1
Indicator	Power and PNP LED
Connector Type	12-pin M12 quick-disconnect
IP Rating	IP67
Includes	Marking tags

Agency Approvals

UL Listed File #	E201820
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement