

8000-88590-0000000 Cut Sheet



Exact 12 passive distribution block, 8 ports, 5-pin M12 sockets, 5-wire, 24 VDC, 4A, power and PNP LED indicator(s), panel mount plug in, IP67. Terminal blocks and marking tags included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/8000-88590-0000000>

Technical Specifications

Brand	Exact 12
Item	Passive distribution block
Number of Ports	8
Socket Type	5-pin M12
Wires Per Socket	5-wire
Socket Current	4A
I/O Per Socket	2
Voltage Rating	24 VDC
Number Of Commons	2
Load Current	8A/common
Indicator	Power and PNP LED
Connector Type	Panel mount plug in
IP Rating	IP67
Includes	Terminal blocks and marking tags

Agency Approvals

UL Listed File #	E201820
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement