

831006 Cut Sheet



Murrplastik EWT-PA two-piece split flexible electrical conduit, polyamide, M16/P11 trade size, black, 82ft/25m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/831006>

Technical Specifications

| | |
|----------------------------|----------------------|
| Brand | Murrplastik |
| Item | Electrical conduit |
| Series | EWT-PA |
| Liquid-tight | No |
| Conduit Type | Two-piece split |
| Flexibility | Flexible |
| Inner Core Material | Modified polyamide 6 |
| Outer Material | Modified polyamide 6 |
| Trade Size | M16/P11 |
| Color | Black |
| Coil Length | 82ft/25m |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/831006.pdf>
See store item page for other formats.