

838516 Cut Sheet



Murrplastik EW-PAB solid flexible corrugated tubing, modified polyamide 6, M20/P16 tubing size, black, 164ft/50m coil length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/838516>

Technical Specifications

Brand	Murrplastik
Series	EW-PAB
Item	Corrugated tubing
Tubing Type	Solid
Flexibility	Flexible
Liquid-tight	No
Material	Modified polyamide 6
Tubing Size	M20/P16
Color	Black

Coil Length	164ft/50m
IP Rating	IP54 IP65
Flammability	UL 94 V-0
Operating Temperature	-49 to +248 °F (-45 to +120 °C)
UV Resistant	Yes
Flexural Fatigue	>11000 Cycles per IEC EN 61386
Crush Resistance	>74 lbf (330 N) 50x50mm per IEC EN 61386 M25/P21 @23C
Applicable Standards	UL 1696

Agency Approvals

UL Recognized File #	E148958
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/838516.pdf>
See store item page for other formats.