

# 84010001 Cut Sheet



GAM helical pinion, Module 1.5, 20 tooth, set screw mount. For use with SureGear PGCN23 series gearboxes.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/84010001>

## Technical Specifications

Brand	GAM
Item	Pinion
Tooth Profile	Helical
Pressure Angle	20 degrees
Module	1.5
Pitch Diameter	31.831mm
Number of Teeth	20
Travel per Rotation	100mm

Maximum Force Feed	1.3 kN
Mounting	Set screw
Mounting Distance	31.4mm
Material	4140 carbon steel
Hardness	55 - 60 HRC
Finish	Ra 0.8
Precision Grade	ISO Q06
For Use With	SureGear PGCN23 series gearboxes

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/84010001.pdf>  
See store item page for other formats.